

Measurement

Mechanical Stopwatch Timer for Timekeeping in Sports and Competitions Timing



Edusupports

www.edusupports.com

sales@edusupports.com

Mechanical Stopwatch Timer for Timekeeping in Sports and Competitions Timing

Mechanical Stopwatch Timer has a rugged stainless-steel case and a chain hook. One button function, starts, stops and resets by consecutive crown depressions, feels good and is easy to operate. The large dial display and clear readings help you easily perform timing work. This Mechanical Stopwatch Timer is wound up by hand. This Mechanical Stopwatch Timer can maintain normal operation in the -10°C to +40°C temperature range. Carry bag and neck strap are included. No battery required.



SKU: 0201110220-01

Mechanical Stopwatch Timer 15 Minutes 30 Seconds
per Circle No Pause 0.1 Second Minimum Scale

Highlights:

Minute hand scale:15 minutes/circle

Second hand scale:30 seconds/circle

Minimum Scale Value: 0.1 second

Continuous Travel Time: ≥ 6 hours

Start, stop & reset by depressing the crown

Start/ stop trigger with winding button

Manual winding

No pause

Dimensions: ϕ 50x68x16mm

EDUSUPPORTS.COM

enhance your mind

Mechanical Stopwatch Timer 15 Minutes 30 Seconds
per Circle with Pause 0.1 Second Minimum Scale

Highlights:

Minute hand scale:15 minutes/circle
Second hand scale:30 seconds/circle
Minimum Scale Value: 0.1 second
Continuous Travel Time: ≥ 6 hours
Start, stop by depressing the crown
Reset by depressing the side button
Start/ stop trigger with winding button
Manual winding
With pause
Dimensions: $\phi 50 \times 68 \times 16$ mm



SKU:0201110220-02

Mechanical Stopwatch Timer 30 Minutes 60 Seconds
per Circle No Pause 0.2 Second Minimum Scale

Highlights:

Minute hand scale:30 minutes/circle
Second hand scale:60 seconds/circle
Minimum Scale Value: 0.2 second
Continuous Travel Time: ≥ 12 hours
Start, stop & reset by depressing the crown
Start/ stop trigger with winding button
Manual winding
No pause
Dimensions: $\phi 50 \times 68 \times 16$ mm



SKU:0201110220-03

EDUSUPPORTS.COM

enhance your mind

Mechanical Stopwatch Timer 30 Minutes 60 Seconds
per Circle with pause 0.2 Second Minimum Scale

Highlights:

- Minute hand scale:30 minutes/circle
- Second hand scale:60 seconds/circle
- Minimum Scale Value: 0.2 second
- Continuous Travel Time: \geq 12 hours
- Start, stop by depressing the crown
- Reset by depressing the side button
- Start/ stop trigger with winding button
- Manual winding
- With pause
- Dimensions: ϕ 50x68x16mm



SKU:0201110220-04

Mechanical Stopwatch Timer 30 Minutes 60 Seconds
per Circle with Pause 0.2 Second Minimum Scale

Highlights:

- Minute hand scale:30 minutes/circle
- Second hand scale:60 seconds/circle
- Minimum Scale Value: 0.2 second
- Continuous Travel Time: \geq 12 hours
- Start, stop by depressing the crown
- Reset by depressing the side button
- Start/ stop trigger with winding button
- Manual winding
- No pause
- Dimensions: ϕ 50x68x16mm



SKU:0201110220-05

EDUSUPPORTS.COM

enhance your mind

Mechanical Stopwatch Timer 15 Minutes 30 Seconds
per Circle with Pause 0.1 Second Minimum Scale

Highlights:

- Minute hand scale:15 minutes/circle
- Second hand scale:30 seconds/circle
- Minimum Scale Value: 0.1 second
- Continuous Travel Time: ≥ 6 hours
- Start, stop by depressing the crown
- Reset by depressing the side button
- Start/ stop trigger with winding button
- Manual winding
- With pause
- Dimensions: $\phi 50 \times 68 \times 16 \text{mm}$



SKU:0201110220-06



SKU:0201110220-07

Mechanical Stopwatch Timer Desk Stopwatch 30
Minutes 30 Seconds per Circle with pause 0.1 Second
Minimum Scale

Highlights:

- Minute hand scale:30 minutes/circle
- Second hand scale:30 seconds/circle
- Minimum Scale Value: 0.1 second
- Start, stop by depressing the crown
- Reset by depressing the crown
- Start, stop by depressing the side button
- Manual winding
- With pause
- Dimensions: L85xH95xD40mm

EDUSUPPORTS.COM

enhance your mind

Mechanical Stopwatch Timer Desk Stopwatch 60
Minutes 60 Seconds per Circle with pause 0.2 Second
Minimum Scale

Highlights:

Minute hand scale:60 minutes/circle

Second hand scale:60 seconds/circle

Minimum Scale Value: 0.2 second

Start, stop by depressing the crown

Reset by depressing the crown

Start, stop by depressing the side button

Manual winding

With pause

Dimensions: L85xH95xD40mm



SKU:0201110220-08